

Low Bay & High Bay Lighting

Features

- Lightweight hanging solution
- 60° beam angle
- Integral driver
- Hanging loop included
- Flicker free
- Fitted with 2 meters of flex
- IP65 rating
- Suitable for indoor use

RS PRO 100W LED Dual Bay Lighting

RS Stock No: 231-8133, 231-8134



RS PRO Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Low Bay & High Bay Lighting

Product Description

Use our high bay lighting to create a unique look and feel within your warehouse, garage, barn or studio. These stylish high bay lights are ideal for illuminating areas while providing an energy-saving retrofit solution. Upon inspection, they are manufactured with a die-cast aluminium body, polycarbonate lens and fitted with 2 metres of flex. There are two light colour options, 4000K (cool white) and 6500K (daylight), and both produce excellent quality lightning

General Specifications

Type	High Bay
Lamp Type	LED
Wattage	100 W
Voltage Rating	220 → 240 V ac
Dimmable	No
Luminosity	12000 lm
Colour Temperature	4000K or 6500K

Variants

RS PRO Dual-Bay High Bay Lighting - 100 W, 4000K	RS stock no: 231-8133
RS PRO Dual-Bay High Bay Lighting - 100 W, 6500K	RS stock no: 231-8134