

Electrical Insulating Gloves Class 00 - RIG0014B

Comfortable electrical protection gloves, combining safety, durability and flexibility

Previously known as: E015B



Electrical



Light Duty

Durable, form-fitting electrical safety gloves, assuredly protecting wearers*

- **Improved durability and flexibility:** ActivArm® Electrical Insulating Gloves Class 00 - RIG0014B are made of durable, flexible latex, using an eco-conscious dipping process
- **Advanced ergonomics:** These insulated gloves' hand-at-rest design and non-splayed fingers limit hand fatigue
- **Elevated comfort:** Their spacious flared cuff enhances ventilation and makes room for clothing
- **Increased practicality:** These electrical protection gloves' smooth, case-hardened finish makes for easy donning and doffing
- **Specialized defenses:** They are arc flash certified (APC 1 in combination with 96-002 leather protectors) and tolerate a touch voltage maximum of AC 500 V (DC 750 V)
- **Certified protection:** These electrical insulated gloves meet relevant CSA, NFPA and OSHA standards, as well as EN standards for acid, ozone and low temperature resistance*
*Category A, Z and C respectively



Industries

- Automotive
- Electrical
- Construction
- Mining
- Machinery and Equipment

Applications

- Applications with risk of touch voltage
- Electrical Contractors
- Hybrid engine manufacturing and repair
- Maintenance Repairs and Operations in all industrial environments (MRO)
- Mass Transit Repair and Maintenance
- Power maintenance, repair & transmission
- Telecom repair near electrical wires

Electrical Insulating Gloves Class 00 - RIG0014B

Comfortable electrical protection
gloves, combining safety, durability
and flexibility

Previously known as: E015B

Key Features

- **Natural rubber latex formulation:** Assured flexibility and durability
- **Ergonomic design:** Better dexterity, less hand fatigue
- **Generous flared cuff:** Enhanced room for clothing and ventilation
*Arc flash certified as per IEC 614821-2:2014 and ASTM F2675:2021 standards

Performance Standards & Regulatory Compliance



Specifications

BRAND STYLE	DESCRIPTION	Gauge	SIZE	LENGTH	COATING COLOR	PACKAGE
ActivArm Electrical Insulating Gloves Class 00 - RIG0014B	Coating Material: Natural Rubber Latex Cuff Style: Straight Cuff with rolled beaded edge		7, 8, 8.5, 9, 9.5, 10, 10.5, 11, 12	360mm/14inch	Black	1 pair/pack, 10 pairs/carton

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 900
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Canada

Ansell Canada
105 Lauder
Cowansville, QC J2K 2K8
Canada
T: +1 800 363 8340
F: +1 800 267 3551

Australia

Ansell Limited
Level 3, 678 Victoria Street,
Richmond, Vic, 3121
Australia
T: +61 1800 337 041
F: +61 1800 803 578

Asia Pacific Region

Ansell Global Trading Center
(Malaysia) Sdn Bhd
Prima 6, Prima Avenue
Block 3512, Jalan Teknokrat 6
T: +603 8310 6688
F: +603 8310 6699