

Number of contacts

4



Identification	Part number		Drawing	Dimensions in mm
	Male insert (M)	Female insert (F)		
Crimp terminal Order crimp contacts separately	09 14 004 3041	09 14 004 3141		

Han Modular

Identification	Wire gauge (mm²)	Part number		Drawing	Dimensions in mm															
		Male contact	Female contact																	
Crimp contacts Power contacts silver plated 	1.5 2.5 4 6	09 32 000 6104 09 32 000 6105 09 32 000 6107 09 32 000 6108	09 32 000 6204 09 32 000 6205 09 32 000 6207 09 32 000 6208		<table border="1"> <thead> <tr> <th>Wire gauge</th> <th>∅</th> <th>Stripping length</th> </tr> </thead> <tbody> <tr> <td>1.5 mm²</td> <td>AWG 16</td> <td>1.75</td> </tr> <tr> <td>2.5 mm²</td> <td>AWG 14</td> <td>2.25</td> </tr> <tr> <td>4 mm²</td> <td>AWG 12</td> <td>2.85</td> </tr> <tr> <td>6 mm²</td> <td>AWG 10</td> <td>3.5</td> </tr> </tbody> </table>	Wire gauge	∅	Stripping length	1.5 mm²	AWG 16	1.75	2.5 mm²	AWG 14	2.25	4 mm²	AWG 12	2.85	6 mm²	AWG 10	3.5
Wire gauge	∅	Stripping length																		
1.5 mm²	AWG 16	1.75																		
2.5 mm²	AWG 14	2.25																		
4 mm²	AWG 12	2.85																		
6 mm²	AWG 10	3.5																		