



LV-MSP-70-SS

Ruland LV-MSP-70-SS, 70mm Two-Piece Shaft Collar with Clamping Lever,
303 SS Collar with Zinc Plated Lever, 98mm OD, 19mm Width



Description

Ruland LV-MSP-70-SS is a two-piece quick clamping shaft collar with clamping lever with a 70mm bore, 98mm OD, and 19mm width. It is made from MSP-70-SS and LF63-CL-M8:37.5-ZS. The clamp style design does not mar the shaft, is easy to remove, and is indefinitely adjustable. The threaded stud on the lever is used in place of standard collar hardware. Two-piece shafts collars can be assembled in-lace without the need to remove other components. Ruland mates halves throughout the manufacturing process for proper fit, alignment, and holding power. When combined, the two parts create a shaft collar that requires no tools to install, remove, or reposition and is ideally suited for packaging, printing, and other applications where frequent setup changes and adjustments are needed. Once the lever is installed in the shaft collar, users simply turn the lever until they meet their desired torque. The adjustable lever can be reposition by the user without the loss of holding power by lifting the handle and twisting it 40° to lock it in a new position. This allows for use in space constrained environments where 360° rotation is not possible to fully seat the lever. MSP-70-SS is made from 303 stainless steel. LF63-CL-M8:37.5-ZS has a zinc plated steel handle and stainless steel threaded stud. This material combination allows for a durable quick clamping and release component with high corrosion resistance that is suitable for most industrial applications. The lever is black to seamlessly integrate with the aesthetics of most equipment. MSP-70-SS is manufactured by Ruland and LF63-CL-M8:37.5-ZS is manufactured by Otto Ganter. LV-MSP-70-SS is RoHS3 and REACH compliant.

Product Specifications

Bore (B1)	70 mm	Bore Tolerance	+0.050 mm / +0.012 mm
Outer Diameter (OD)	98 mm	Center to Lever Top H1	71.9 mm
Width (W)	19 mm	Width Tolerance	+0.076 mm / -0.254 mm
Lever Length L1	63 mm	Lever Height H2	62 mm
Hub Diameter DH	17.5 mm	Sleeve Length L2	37.5 mm
Recommended Gap	3.18 mm	Recommended Shaft Tolerance	+0.000 mm / -0.013 mm
Thread TH	M8	Hex Wrench Size	6.0 mm
Seating Torque	23 Nm	Screw Location (R)	42.01 mm
Number of Screws	2 ea	Collar Part Number	MSP-70-SS
Lever Part Number	LF63-CL-M8:37.5-ZS	Collar Material	303 Stainless Steel
Collar Finish	Bright	Handle Color	Black
Handle Material	Zinc	Handle Finish	Powder Coated
Insert and Screw Material	303 Stainless Steel	Manufacturer	Ruland Manufacturing
Country of Origin	Shaft Collar - USA Lever - Germany	Weight (lbs)	1.341076

UPC	63452937524	Tariff Code	8483.60.8000
UNSPC	31162811		
Note 1	Performance ratings are for guidance only. The user must determine suitability for a particular application.		
Prop 65	WARNING This product can expose you to the chemical Soots, Benzene, Lead, Nickel (metallic), known to the State of California to cause cancer, and Lead and Benzene known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov .		