

PP-V4-OUT-IDC-RJ45-8P-J-P-WH, AWG 24-22



Image is for illustration purposes only. Please refer to product description.

Part number	09 45 845 1563
Specification	PP-V4-OUT-IDC-RJ45-8P-J-P-WH, AWG 24-22
HARTING eCatalogue	https://harting.com/09458451563

Identification

Category	Accessories
Series	HARTING PushPull (V4)
Type of accessory	Outlet

Version

Termination method	IDC insulation displacement termination
Shielding	Fully shielded, 360° shielding contact
Fixing	Wall mounting
Pack contents	2-port outlet housing with protection caps
	Cable management
	Cable gland
	Label
	2x RJ45 cable jack 09 45 545 1562
	Assembly instructions

Technical characteristics

Conductor cross-section	0.22 ... 0.32 mm ² Solid
	0.22 ... 0.32 mm ² Stranded
Conductor cross-section [AWG]	AWG 24 ... AWG 22
Wire outer diameter	1.7 mm
Transmission characteristics	Cat. 6 _A Class E _A up to 500 MHz
Data rate	10 Mbit/s
	100 Mbit/s
	1 Gbit/s
	2.5 Gbit/s
	5 Gbit/s
	10 Gbit/s



Pushing Performance
Since 1945

Technical characteristics

Limiting temperature	-20 ... +70 °C
Mating cycles	≥750
Degree of protection acc. to IEC 60529	IP65 IP67
Cable diameter	6 ... 9 mm

Material properties

Material (hood/housing)	Polycarbonate (PC) Fibre-glass reinforced
Colour (hood/housing)	White
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained

Commercial data

Packaging size	1
Country of origin	China
European customs tariff number	85389099
GTIN	5713140235823
eCl@ss	27440292 Connector component (accessories)
ETIM	EC002943
UNSPSC 24.0	39121400