



Hand protection

VENICUTD10

LONG-LASTING CUT WORK

Level D anti-cut glove with extremely fine handling and comfort of use, ideal for dry conditions.



Specific benefits



Easy to use

· Perfect fit so that users do not feel any discomfort in the wrist area with prolonged use



Performance

· Lightweight for optimal dexterity

Applications

- Public works
- Building
- Finishing works / Craftsmanship
- Heavy industry
- Light industry
- Maintenance

Certifications and norms



EN 388
3 2 4 2 D

ANSI ISEA 105

A4

Protects against risks



Cutting



Wearing



enjoy safety

Edit 12/12/2024
www.deltaplus.eu



Hand protection

VENICUTD10

LONG-LASTING CUT WORK

Level D anti-cut glove with extremely fine handling and comfort of use, ideal for dry conditions.

Standards - Details



EN388:2016+A1:2018

3 [0-4] ABRASION RESISTANCE
2 [0-5] CUT RESISTANCE
4 [0-4] TEAR RESISTANCE
2 [0-4] PIERCE RESISTANCE
D [A-F] CUT RESISTANCE ISO 13997

Technical details

Glove kind	Mechanical glove
Glove family	Knitted coated glove
Mechanical glove kind	Knitted
Coating material and finition	PU
Coating level	Palm coated
Number of layer	Single layer
Gauge	21
Benefits element	Touch sensitive, Reach, Vendor pack
Color	Grey
Size	6, 7, 8, 9, 10, 11
Type of packaging	in individual bags



Safety gloves

VENICUTD10

LONG-LASTING CUT WORK

Level D anti-cut glove with extremely fine handling and comfort of use, ideal for dry conditions.

Logistics information

Reference	Colour	Size	Designation	EAN13	Box code			Weight			
VECUTD10GR06	Grey	06	VENICUTD10	3295249296988	13295249296985	60	12	3.1 kg	29.0 cm	53.4 cm	14.8 cm
VECUTD10GR07	Grey	07	VENICUTD10	3295249296995	13295249296992	60	12	3.2 kg	29.0 cm	53.4 cm	15.6 cm
VECUTD10GR08	Grey	08	VENICUTD10	3295249297008	13295249297005	60	12	3.5 kg	29.4 cm	53.8 cm	15.2 cm
VECUTD10GR09	Grey	09	VENICUTD10	3295249297015	13295249297012	60	12	3.5 kg	31.0 cm	55.8 cm	17.2 cm
VECUTD10GR10	Grey	10	VENICUTD10	3295249297022	13295249297029	60	12	3.8 kg	31.2 cm	55.8 cm	17.0 cm
VECUTD10GR11	Grey	11	VENICUTD10	3295249297039	13295249297036	60	12	3.9 kg	31.6 cm	55.4 cm	16.4 cm



Multiple sales



Minimum sales



Box Width



Box Depth



Box Height