



**Application Range**

Glass fibre-reinforced for maximum mechanical stability. Supporting surface for spanner means scratches on the housing are avoided.

**Technical Data**

Material: Polyamide, glass fibre-reinforced  
Temperature range: -20°C to +100°C

**Article List**

Part Number	Description	Thread Size	Colour
53019001	SKINTOP PG Thread Nylon Locknut	PG7	Light Grey
53019011	SKINTOP PG Thread Nylon Locknut	PG9	Light Grey
53019021	SKINTOP PG Thread Nylon Locknut	PG11	Light Grey
53019031	SKINTOP PG Thread Nylon Locknut	PG13.5	Light Grey
53019041	SKINTOP PG Thread Nylon Locknut	PG16	Light Grey
53019051	SKINTOP PG Thread Nylon Locknut	PG21	Light Grey
53019061	SKINTOP PG Thread Nylon Locknut	PG29	Light Grey
53019071	SKINTOP PG Thread Nylon Locknut	PG36	Light Grey
53019081	SKINTOP PG Thread Nylon Locknut	PG42	Light Grey
53019091	SKINTOP PG Thread Nylon Locknut	PG48	Light Grey

Part Number	Description	Thread Size	Colour
53019003	SKINTOP Metric Thread Nylon Locknut	M12	Light Grey
53019013	SKINTOP Metric Thread Nylon Locknut	M16	Light Grey
53019023	SKINTOP Metric Thread Nylon Locknut	M20	Light Grey

53019033	SKINTOP Metric Thread Nylon Locknut	M25	Light Grey
53019043	SKINTOP Metric Thread Nylon Locknut	M32	Light Grey
53019053	SKINTOP Metric Thread Nylon Locknut	M40	Light Grey
53019063	SKINTOP Metric Thread Nylon Locknut	M50	Light Grey
53019073	SKINTOP Metric Thread Nylon Locknut	M63	Light Grey