



### KAA-0760



Die profile



Crimp profile

The KAA-0760 is a precision, ratchet crimp tool designed to provide consistent and reliable crimp connections on Red, Blue, Yellow insulated terminals on wires ranging from 0,5-6,0 mm<sup>2</sup>.

#### Easy to use

Open the tool. Insert terminal in correct nest. Close tool until terminal fastened. Insert wire into terminal. Close tool until ratchet release. Attention: To release ratchet mechanism, push the trigger.

#### Calibration

To calibrate this tool the pre-load has to be measured. Gauge is required to ensure that the die is according to specification. For more information; See instruction sheet.

- Asymmetric dies give optimised crimps on the wires conductors and insulation.
- The dies mark to terminal so that they can be inspected for correct use of the tool.
- Ergonomic handles allowing two handed operation for powerful, low effort crimping.
- Ratchet action to ensure full crimp cycle with safety release.
- Durable - minimum of 50,000 cycles.
- Tool is factory set with a precise eccentric cam adjustment function to guarantee performance.

#### Technical data

Prod.code:	KAA-0760
Length:	255 mm / 10,04"
Height:	72 mm / 2,83"
Weight:	560 gr / 1,23 lbs
Connector:	Pre-insulated
Description:	Red, Blue, Yellow
Wire size:	0,5-6,0 mm <sup>2</sup>

Distributors address info