



insta contactor with 3 NO contacts and 1 NC contact for 230 V AC, 400 V 25 A control 24 V AC

Figure similar

Model	
product brand name	SENTRON
product designation	Installation contactor
design of the product	3 NO contacts 1 NC contact
General technical data	
relative ON period of magnet coil	100 %
type of voltage of the operating voltage	AC
type of voltage of the operating voltage for actuation	AC
Supply voltage	
operating voltage rated value	
• minimum	440 V
• maximum	440 V
Protection class	
protection class IP	IP20
Breaking Capacity	
switching capacity active power with incandescent lamp load	2 000 W
Dissipation	
power loss [W] for rated value of the current at AC in hot operating state per pole	2.2 W
Control current	
control supply voltage	
• rated value	24 V
• rated value maximum	24 V
Product details	
product component slide for manual operation	No
number of NC contacts	1
number of NO contacts	3
product extension installable supplementary devices	Yes
Connections	
installation or assembly note	provision must be made for spacers to ensure heat dissipation
Mechanical Design	
height	90 mm
width	36 mm
depth	71 mm
installation depth	70 mm
number of modular width units	2
Net Weight	262 g

Approvals Certificates

Environmental Product Declaration

• global warming potential [CO2 eq] / during manufacturing	1.36 kg
• global warming potential [CO2 eq] / during sales	0.051 kg
• global warming potential [CO2 eq] / during operation	211 kg
• global warming potential [CO2 eq] / after end of life	-0.106 kg
• global warming potential [CO2 eq] / total	212 kg

Environment

General Product Approval



[Environmental Con-
firmations](#)

[Environmental Con-
firmations](#)



[Confirmation](#)



General Product Approval

Test Certificates

other



[Miscellaneous](#)



[Special Test Certific-
ate](#)



[Confirmation](#)

Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information for data generation and storage

<https://support.industry.siemens.com/cs/ww/en/view/109995012>

Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=5TT5831-2>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/5TT5831-2>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

https://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=5TT5831-2

CAX-Online-Generator


<https://www.siemens.com/cax>

Tender specifications

<https://www.siemens.com/specifications>

Characteristic curves

[https://curves.simarisiemens.com/curves/<mmp_prod_noCOMP="HAUPT"></mmp_prod_no>](https://curves.simarisiemens.com/curves/<mmp_prod_noCOMP=)



last modified:

8/13/2025 

