

Comb busbars for DPN

		Comb busbar			Lateral tooth-caps	Tooth-caps	Insulated connectors
Catalogue numbers	2-pole	21086	21088	21089	21094	21096	21098
	3-pole	21090	21092	21093	21095	21096	21098
Characteristics		24 modules (9 mm)	48 modules (9 mm)	96 modules (9 mm)	-	6 modules (9 mm)	-
		12 modules (18 mm)	24 modules (18 mm)	48 modules (18 mm)	-	3 modules (18 mm)	-
		Rating: 80 A Quantity per catalogue numbers: 1			Set of 40	Set of 12	Set of 4 For 25 mm ² cable
Supplied accessories		4 lateral tooth-caps		0	-	-	-
		1 tooth-caps	2 tooth-caps	0	-	-	-

Comb busbars for C60 and iC60

		Comb busbar		Lateral tooth-caps	Tooth-caps	Insulated connectors
Catalogue numbers	1-pole	14881	14891	14886	14888	14885
	2-pole	14882	14892	14886	14888	14885
	3-pole	14883	14893	14887	14888	14885
	4-pole	14884	14894	14887	14888	14885
Characteristics		■ 24 modules (9 mm) ■ 12 modules (18 mm) ■ 1 piece	■ 48 modules (9 mm) ■ 24 modules (18 mm) ■ Set of 2	Set of 40	Set of 40	Set of 4 For 25 mm ² cable
		Rating: 80 A with 1 supply point 100 A with 2 supply points				
Supplied accessories		2 lateral tooth-caps		-	-	-

Comb busbars for C120 and NG125

		Comb busbar		Lateral tooth-caps + tooth-caps
Catalogue numbers	1-pole		14811	14818
	2-pole		14812	14818
	3-pole	14813		14818
	4-pole		14814	14818
Characteristics		■ 45 modules (9 mm) ■ 22.5 modules (18 mm) ■ 1 piece	■ 48 modules (9 mm) ■ 24 modules (18 mm) ■ Set of 1	4 lateral tooth-caps + 20 tooth-caps
	Rating: 125 A 63 A maxi by outgoers			
Supplied accessories		Tooth-caps (8 for 1 and 2-pole, 4 for 1 and 2-pole) 2 lateral tooth-caps		-