



ENGLISH

Datasheet

Stock No. 918-6412

RS Pro 6 piece M42 Bi-metal Thinwall Holesaw Kit



Specifications:

Article No. 918-6412

Material: M42 Cobalt 8% Bi-metal

Shank Dia.: 1/4" quick change shank

Cutting depth: 12mm

Set Contents: 16-20-25-32-40-51mm

Features:

It is ideal for the electrical and plumbing tradesman. Holesaw has a thin 0.5mm sidewall blade thickness, which allows for faster cutting and longer better life.

M42 Cobalt Bi-metal is for long life.

Self ejecting plug removal

Application:

Suitable for cutting wood, plastic and thin sheet metal such as max. thickness 0.5mm stainless steel, max. thickness 2mm mild steel, max. thickness 2mm aluminium .

Perfect for use with 9.6v above chargeable impact driver, chargeable electrical portable drill and electric portable drill (below 400w). Please don't use with impact drill and impact hammer.