



ASP-AS-C36-JT-M

Medium Cut Pole Pruning Saw 360 mm








PRODUCT DETAILS

- Product is suitable for the applications; pruning, trimming, gardening, arborist and forestry
- Precision ground, razor sharp JT teething provides smooth cutting and perfect result
- Strong 360 mm blade with 6,2 TPI (medium teething) for most sized branches
- Sheath in impact-resistant plastic with quick locking and thumb grip release and belt loop
- Easier cutting of branches at height when attached to the section pole or short telescopic pole
- Reduced friction and concentrated cutting energy from the taper ground blade teething
- Hook at tip of blade to prevent slipping out of kerf
- Bark breaking blade at joint of the blade and adaptor
- The tooth tip hardened curved blade is flexible, yet stable and long lasting
- Connection adaptor for the ASP-1850 pole system, length: C36, 360 mm



PRODUCT ATTRIBUTES

Product					
ASP-AS-C36-JT-M	360 mm	14-1/4 in	6.2	283 g	10 oz

Follow the Fish!

