

## FEATURES

- **Heavy Duty Design:** Provides a tensile strength of 114 kg, ensuring secure fastening of large cable bundles.
- **Nylon Material:** Offers durability and resistance to wear, suitable for demanding environments.
- **UL 94 V-2 Fire Behaviour:** Meets fire safety standards, reducing risk in high-temperature applications.
- **Large Bundle Capacity:** Accommodates a maximum bundle diameter of 473 mm, ideal for extensive cable management.
- **Temperature Resistance:** Operates effectively up to 85 °C, suitable for various industrial settings.
- **Wide Width:** 12.7 mm width provides additional stability and support for heavy cables.
- **Standards Compliant:** Meets multiple standards including ABS, CE, cULus, DNV, LR, RoHS, and VDE, ensuring quality and safety.

## RS PRO Heavy Duty Cable Tie, 1530 mm Nylon

RS Stock No: 656-115



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

### Product Description

The RS PRO Heavy Duty Cable Tie is designed for securing and organising large bundles of cables or wires. With a length of 1530 mm, it is ideal for industrial applications where robust and reliable cable management is essential. Made from durable nylon, it offers a strong and long-lasting solution.

### General Specifications

Colour	Natural
Product Type	Cable Tie
Sub Type	Heavy Duty Cable Tie
Tensile Strength	114 kg

### Protection Category

Fire Behaviour	UL 94 V-2
UV Resistant	No

### Mechanical Specifications

Length	1530 mm
Material	Nylon
Maximum Bundle Diameter	473 mm
Width	12.7 mm

### Operation Environment Specifications

Maximum Operating Temperature	85 °C
-------------------------------	-------

### Approvals

Standards/Approvals	ABS 15-TA1338482-PDA, CE 40022513, cULus E97527, DNV TAE00000US, LR 16-80006, RoHS, UL94V-2, VDE 40022513
---------------------	---