






|                                                                                     |  |                                              |  |                                    |  |                            |  |                 |  |                    |  |                                                          |  |
|-------------------------------------------------------------------------------------|--|----------------------------------------------|--|------------------------------------|--|----------------------------|--|-----------------|--|--------------------|--|----------------------------------------------------------|--|
|  |  | All Dimensions in mm<br>Original Size DIN A4 |  | Scale<br>1:1                       |  | Free size tol.             |  | Ref.            |  |                    |  |                                                          |  |
|                                                                                     |  |                                              |  |                                    |  |                            |  | Sub.            |  |                    |  |                                                          |  |
|  |  | All rights reserved                          |  | Created by<br>HELLMANN             |  | Inspected by<br>LOETKEMANN |  | Standardisation |  | Date<br>2024-03-07 |  | State<br>Final Release                                   |  |
| HARTING<br>D-32339 Espelkamp                                                        |  | Department EL PD                             |  | Title<br>Han F+B hood-gg-M25 black |  |                            |  |                 |  |                    |  | Doc-Key / ECM-Nr.<br>100780093/UGD/001/F<br>500000264896 |  |
|                                                                                     |  |                                              |  | Type<br>TB                         |  | Number<br>19 15 503 1403   |  |                 |  |                    |  | Rev.<br>F                                                |  |