

Datasheet ECP-6 Series

6w Multi Head Plug In Power Supply

ENGLISH



Features

- Universal input
- No load power consumption
- Compact and light-weight plastic case
- Protections: Short circuit/ Overload
- Class II power supply (without earth pin)
- Pass LPS
- 1 Year warranty

Model		816-0116	816-0119	816-0113
Input	Input Voltage Range	100-240VAC		
	Input Frequency Range	47Hz to 63Hz		
	No Load Power Consumption	0.3W Max		
	In-Rush Current	50A Max		
	Input Current	0.8A Max		
Output	Output Voltage	+12V	+15V	+24V
	Output Load Range	0.01-0.5A	0.01-0.4A	0.01-0.25A
Environment	Efficiency	≤83%		
	Working Temperature	0°C-40°C		
	Working Humidity	10%-95%		
Safety	EMI	EN55022 (EN61000-3-2, EN61000-3-3)		
	EMC	EN55024 (IEC61000-4-2, IEC61000-4-3, IEC61000-4-4, IEC61000-4-5)		
Dimensions	Size	101x 52x 36mm		

