

ENGLISH

Datasheet

Buzzer ,24 V dc, 95dB at 1 Metre

RS Stock number



Specifications:

Supply Voltage: 10-28VDC

Rated Current: 25mA

Decibels at 1 Metre: 95dB

Resonant Frequency: 2900±500Hz

Current Type: DC

Operating Temperature: -20°C to $+60^{\circ}\text{C}$ Storage Temperature: -30°C to $+70^{\circ}\text{C}$

Diameter: 43 mm Colour: Black


Mounting Style: Panel Mount


Housing Material ABS
Application Type: Buzzer



Dimensions:

ENGLISH





Dimensions Unit: mm

Tolerance: ±0.5mm