

1417984

https://www.phoenixcontact.com/gb/products/1417984

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Housing screw connection, Pin, M12, Rear mounting, M14 x 1, THR solder connection, Alternative product in accordance with RoHS II without Exemption 6c (Pb < 0.1 %) item no.: 1239180

Your advantages

- · Easy device integration, thanks to mechanical port screw connections with threaded fastening
- · Flexible PCB assembly: two-piece connectors for wave and THR soldering

Commercial data

Item number	1417984
Packing unit	100 pc
Minimum order quantity	100 pc
Sales key	ABQACB
Product key	ABQACB
GTIN	4055626276977
Weight per piece (including packing)	9.166 g
Weight per piece (excluding packing)	9.166 g
Customs tariff number	85366990
Country of origin	DE



1417984

https://www.phoenixcontact.com/gb/products/1417984

Technical data

Notes

Notes on operation	The electrical and mechanical data specified assume that the connector pair is correctly locked and mounted. If the connector is unlocked and if there is a danger of contamination, the connector must be sealed using a protective cap > IP54. Influences arising from litz wires, cables or PCB assembly must also be taken into consideration.
Order information:	If necessary, order locking nut separately

Product properties

Product type	Panel mounting base
Thread type	M12

Connection data

Connection method	THR solder connection
Tightening torque	2 3 Nm

Material specifications

Material	Brass, nickel-plated
Seal material	FKM
	FKM
Material for screw connection	Brass, nickel-plated

Connector

Connection 1

Head design	Pin
Head thread type	M12

Environmental and real-life conditions

Ambient conditions

Degree of protection (when plugged in)	IP67 (correctly plugged in and locked)
Degree of protection	IP67 (correctly plugged in and locked)
	IP67, when in locked state
Ambient temperature (operation)	-25 °C 85 °C (Plug / socket)
	-40 °C 85 °C (without mechanical actuation)
UL Type Rating	Type 4 (indoor use only)

Standards and regulations

Standard designation	M12 circular connector
Standards/specifications	according to IEC 61076-2-101

Mounting

Mounting type	Rear mounting M14 x 1



1417984

https://www.phoenixcontact.com/gb/products/1417984

Classifications

_			
_	\sim 1		\neg
-		A:	つこつ

	ECLASS-13.0	27440224
E-	ГІМ	
_	I IIVI	
	ETIM 9.0	EC003556
U	NSPSC	
	UNSPSC 21.0	39121100



1417984

https://www.phoenixcontact.com/gb/products/1417984

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)
China RoHS	
Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.
EU REACH SVHC	
REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	468354f4-f0ad-4da8-9c99-1174e8807d53

Phoenix Contact 2025 © - all rights reserved https://www.phoenixcontact.com

PHOENIX CONTACT Ltd Halesfield 13, Telford Shropshire, TF7 4PG 01952 681700 info@phoenixcontact.co.uk