

FEATURES

- Precise Temperature Measurement
- Heating calibration
- Heating/Cooling Modes
- Open Window Detection Feature
- ON/OFF Control
- Wired Connection
- Hysteresis Settings
- Wired Connection
- Backlit LCD Display
- Simple Wall Mount Installation
- Operating Temperature Range of +5°C to +30°C

RS PRO Thermostats

RS Stock No.: 0673045



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

Basic On/Off Thermostat – Reliable Temperature Control Made Simple

Keep your home or workspace comfortable with our easy-to-use On/Off Thermostat. Designed for simplicity and reliability, this thermostat provides straightforward temperature control without the need for complex programming or smart features. Ideal for those who prefer a no-fuss solution, it turns your heating or cooling system on when the room temperature drops below or rises above your setpoint—and off once the desired temperature is reached.

Key Features:

- *Simple Dial or Button Control: Set your preferred temperature with ease—no menus, no Wi-Fi, no apps.*
- *Precise Temperature Switching: Maintains a consistent indoor climate using responsive on/off operation.*
- *Compact & Durable Design: Clean, minimal look fits any room decor and is built to last.*
- *Wide Compatibility: Works with most standard HVAC systems, including gas, electric, and oil heaters.*
- *Energy Efficient: Prevents overuse of your system by shutting off automatically when target temperature is reached.*

Perfect For:

- *Homeowners seeking a no-frills thermostat*
- *Rental properties and vacation homes*
- *Workshops, garages, and utility rooms*
- *Elderly users or those who prefer analog simplicity*

Upgrade to stress-free comfort with a thermostat that does exactly what you need—no more, no less

General Specifications

Product Type	Wired Programmable Thermostat; Active Heating Thermostat
Program Duration	7h; 24days
Switch Configuration	SPST
Temperature Range	+5°C to + 30°C
Maximum Temperature	30°C
Minimum Temperature	+5°C
Display Type	Backlit LCD
Sensors	Temperature

Colour	White; Black
Additional Features	Backlight; Manual Override
Applications	Construction areas, Home security

Electrical Specifications

Supply Voltage	230V	
Battery	2 x AA Batteries Required	
Contact Rating	Heat	Cool
	7A	7A
Contact Voltage	230V	
Operation	Button; Turn	

Mechanical Specifications

Mounting Method	Surface mounted
Height	85,7 mm
Width	85,7 mm
Depth	33,5 mm

Operation Environment

Ambient Temperature	+40°C maximum
---------------------	---------------

Approvals

Compliance/Certifications	CE / EMC / LVD / RED
Declarations	RoHs,Reach