



Top and side entry hoods with knurled screws

Identification	No. of contacts	Part No.	Drawing	Dimensions in mm																																				
Top entry hood Black thermoplastic	9 15 25 37 50	09 67 009 0424 09 67 015 0424 09 67 025 0424 09 67 037 0424 09 67 050 0424		<table border="1"> <thead> <tr> <th></th> <th>A</th> <th>B</th> <th>C</th> <th>D</th> <th>max. Ø</th> </tr> </thead> <tbody> <tr> <td>9</td> <td>30.5</td> <td>15</td> <td>38</td> <td>49</td> <td>8.5</td> </tr> <tr> <td>15</td> <td>41.0</td> <td>15</td> <td>38</td> <td>49</td> <td>11.5</td> </tr> <tr> <td>25</td> <td>54.5</td> <td>15</td> <td>40</td> <td>49</td> <td>11.5</td> </tr> <tr> <td>37</td> <td>71.0</td> <td>15</td> <td>40</td> <td>49</td> <td>11.5</td> </tr> <tr> <td>50</td> <td>67.5</td> <td>19</td> <td>40</td> <td>49</td> <td>14.0</td> </tr> </tbody> </table>		A	B	C	D	max. Ø	9	30.5	15	38	49	8.5	15	41.0	15	38	49	11.5	25	54.5	15	40	49	11.5	37	71.0	15	40	49	11.5	50	67.5	19	40	49	14.0
	A	B	C	D	max. Ø																																			
9	30.5	15	38	49	8.5																																			
15	41.0	15	38	49	11.5																																			
25	54.5	15	40	49	11.5																																			
37	71.0	15	40	49	11.5																																			
50	67.5	19	40	49	14.0																																			
Top entry hood Metallized thermoplastic	9 15 25 37	09 67 009 0425 09 67 015 0425 09 67 025 0425 09 67 037 0425		<table border="1"> <thead> <tr> <th>max. Ø</th> </tr> </thead> <tbody> <tr> <td>3.3</td> </tr> <tr> <td>4.3</td> </tr> <tr> <td>5.3</td> </tr> <tr> <td>6.3</td> </tr> </tbody> </table> <table border="1"> <thead> <tr> <th>max. Ø</th> </tr> </thead> <tbody> <tr> <td>7.3</td> </tr> <tr> <td>8.3</td> </tr> <tr> <td>9.3</td> </tr> <tr> <td>10.3</td> </tr> </tbody> </table> <p>Cut appropriate cable entry to fit actual cable diameter</p>	max. Ø	3.3	4.3	5.3	6.3	max. Ø	7.3	8.3	9.3	10.3																										
max. Ø																																								
3.3																																								
4.3																																								
5.3																																								
6.3																																								
max. Ø																																								
7.3																																								
8.3																																								
9.3																																								
10.3																																								
Top and side entry hood Black thermoplastic	9 15 25 37	09 67 009 0434 09 67 015 0434 09 67 025 0434 09 67 037 0434 ²⁾		<table border="1"> <thead> <tr> <th></th> <th>A</th> <th>B</th> <th>C</th> </tr> </thead> <tbody> <tr> <td>9</td> <td>31.5</td> <td>15</td> <td>40.0</td> </tr> <tr> <td>15</td> <td>40.0</td> <td>15</td> <td>40.0</td> </tr> <tr> <td>25</td> <td>53.5</td> <td>15</td> <td>43.0</td> </tr> <tr> <td>37</td> <td>71.3</td> <td>15</td> <td>42.5</td> </tr> </tbody> </table>		A	B	C	9	31.5	15	40.0	15	40.0	15	40.0	25	53.5	15	43.0	37	71.3	15	42.5																
	A	B	C																																					
9	31.5	15	40.0																																					
15	40.0	15	40.0																																					
25	53.5	15	43.0																																					
37	71.3	15	42.5																																					
Top and side entry hood¹⁾ Metallized thermoplastic	9 15 25 37	09 67 009 0435 09 67 015 0435 09 67 025 0435 09 67 037 0435 ²⁾		<table border="1"> <thead> <tr> <th></th> <th>A</th> <th>B</th> <th>C</th> </tr> </thead> <tbody> <tr> <td>9</td> <td>31.5</td> <td>15</td> <td>40.0</td> </tr> <tr> <td>15</td> <td>40.0</td> <td>15</td> <td>40.0</td> </tr> <tr> <td>25</td> <td>53.5</td> <td>15</td> <td>43.0</td> </tr> <tr> <td>37</td> <td>71.3</td> <td>15</td> <td>42.5</td> </tr> </tbody> </table>		A	B	C	9	31.5	15	40.0	15	40.0	15	40.0	25	53.5	15	43.0	37	71.3	15	42.5																
	A	B	C																																					
9	31.5	15	40.0																																					
15	40.0	15	40.0																																					
25	53.5	15	43.0																																					
37	71.3	15	42.5																																					
Grommet for top and side entry black thermoplastic hood (15, 25, 37 ways)		09 67 001 9968		<table border="1"> <thead> <tr> <th>Ø</th> </tr> </thead> <tbody> <tr> <td>3.3</td> </tr> <tr> <td>4.3</td> </tr> <tr> <td>5.3</td> </tr> <tr> <td>6.3</td> </tr> </tbody> </table>	Ø	3.3	4.3	5.3	6.3																															
Ø																																								
3.3																																								
4.3																																								
5.3																																								
6.3																																								

D-Sub - H

¹⁾ Not normally kept in stock
²⁾ 37 ways is only side entry