



All dimensions are in mm; tolerances according to ISO 2768 m-H

Description

Fast and secure installation in splice panels.
Easy, fast and secure handling with transparent bundle jacket.

Error-free, fast identification and allocation of fibers to the assembly connectors inside the cassette due to 12 different colors coding of the fibers and their buffer jackets

Cable type

12 Fiber pigtail-bundle, cable
Dry loose 900µm buffered LB900

Color

12 different colors according to DIN VDE0888 color coding standards and transparent bundle jacket

Fiber type

S/M G652D or G657A

Pigtail Length

3.0m

Connector

E2000 HRL

Dieses Dokument ist urheberrechtlich geschützt • This document is protected by copyright • Rosenberger Hochfrequenztechnik GmbH & Co. KG
RF_35/06:10/1.0

Packing

Standard: 1 pce in a plastic bag

Dieses Dokument ist urheberrechtlich geschützt • This document is protected by copyright • Rosenberger Hochfrequenztechnik GmbH & Co. KG
RF_35/06:10/1.0

While the information has been carefully compiled to the best of our knowledge, nothing is intended as representation or warranty on our part and no statement herein shall be construed as recommendation to infringe existing patents. In the effort to improve our products, we reserve the right to make changes judged to be necessary.

Draft	Date	Approved	Date	Rev.	Engineering change number	Name	Date
Y.Zhang	2015-10-30	U.Albrich	2015-10-30	001	15-0003	Y.Zhang	2015-10-30

Rosenberger Hochfrequenztechnik GmbH & Co. KG P.O.Box 1260 D-84526 Tittmoning Germany www.rosenberger.de	Tel. : +49 8684 18-0 Email : info@rosenberger.de	Page 2 / 2
--	---	---------------