

NTT07

7 Day Slimline Electronic General Purpose Timeswitch

Features & Benefits

- Extra Large Screen With Blue LED Backlighting
- Red LED 'Mains ON' and Green LED 'Output' Indicators For Easy Viewing
- Large Programme Buttons
- Self-Cancelling Override Button To Next Programme Change
- Optional 1 & 2 Hour Boost Button
- Automatic Summer/Winter Time Change
- Rechargeable memory back-up
- Voltage Free Contacts



Technical Data

Operating Voltage	230V AC
Frequency	50Hz
Installation Type	Surface Mount
Earth Class Rating	Class II
Operating Temperature	0°C to 40°C
Ingress Protection Rating	IP20
Setting Type	Digital
Battery Type	NiMH 1.2V 80mAh Rechargeable Battery
Power Reserve	672 Hours (28 Days)

Data sheet

NTT07

Time / Immersion & General Purpose Timeswitches

Program Modes	24 Hour/7 Day, 1 Hour/2Hour Boost
Switch type	Single Pole
Voltage Free Contacts	Normally Open, Normally Closed (Changeover)
Mounting Hole Centres (mm)	90
Standby Consumption	<0.96W
Number of Channels	1
Switch rating	16A Resistive , 2400W Halogen, 750W Fluorescent, 100W CFL, 100W LED
Shortest Switching Time	1 Minute
Programmable Slots	4 ON 4 OFF
Permanent ON Facility	Yes (Override ON)
Cable Capacity (mm2)	1.5 - 2.5mm2 Flexible Cable
Cable Entry(s)	Back Entry (Knockouts), Bottom Entry

General

Weight (g)	210
Height (mm)	120
Width (mm)	74
Depth (mm)	46
Body Construction	Polycarbonate
Product Colour	White
Accessories (Included)	Fittings (Rawl Plugs, Screws)
EAN Number	5012483012352
Guarantee Period	3 Years

Data sheet

NTT07

Time / Immersion & General Purpose Timeswitches

Line Diagrams

