

MLFB-Ordering data

6SL3203-0CE21-0AA0



Figure similar

Client order no. :

Order no. :

Offer no. :

Remarks :

Item no. :

Consignment no. :

Project :

Rated data		Connections	
Input		Line side	
Number of phases	3 AC	Version	screw-type terminal
Line voltage	380 ... 480 V	Load side	
Output		Version	screw terminals
Rated current	11.3 A	Conductor cross-section	4.00 mm ² (12 AWG)
Mechanical data		PE connection	
Dimensions		Version	M4 x 8, washer, spring lock washer
Width	125.0 mm (4.9 in)	Standards	
Height	140.0 mm (5.5 in)	Compliance with standards	cURus
Depth	71.0 mm (2.8 in)		
Degree of protection	IP20 / UL open type		
Net weight	2.1 kg (4.6 lb)		