



## Notice : 1549 EPA DK

Index : 3

### GUYARD SAS

22-24, rue Lucien Rouzet  
Z.A. Villedieu sur Indre/Niherne  
36250 NIHERNE FRANCE

### Intermediate risks - Category II PPE

EN ISO 20420 : 2020 EN 388 : 2016 + A 1 : 2018  
EN 407 : 2020 EN ISO 13997 : 1999

EN ISO 21420 : 2020 EN 388 : 2016 + A 1 : 2018 EN 407 : 2020

### FEATURES :

- Repellent cowhide grain leather
- Fully lined with 50% aramid fiber, 50% cotton.
- Equipped with a buttonhole and elastic tightening at the wrist.
- Chrome tanning, sewing 100 aromatic polyamide thread. Length 24 to 27 cm depend on size.

### TAILLE DISPONIBLE :

- Size 8 to 11

### PRECAUTIONS FOR USE:

- Wear the gloves on dry and clean hands. It is recommended to carry out a preliminary test of the gloves. Real conditions of use may differ from EU type tests.
- Before each use, check that the gloves do not have any defects, holes, tears, abnormal wear.
- Expiry date: 5 years from the date of manufacture indicated in the glove.

### SAFETY COMFORT AND DEXTERITY :

- Dexterity level 5.
- The glove does not contain substances at levels that are known or suspected to have adverse effects on the hygiene or health of the user in the conditions of predictable use.

### PACKAGING :

- In case of unpacking, a copy of the instructions must be attached with the smallest packaging.
- Bag of 10 pairs.
- Box of 100 pairs.

### MARKING :

- The CE marking affixed to this glove signifies compliance with the essential health and safety requirements of European Regulation 2016/425 relating to personal protective equipment (PPE).



3 3 3 3 C



4 2 2 X 4 X

### PERFORMANCE LEVELS :

#### EN 388 : 2016 + A 1 : 2018

- |  |     |
|--|-----|
| • Abrasion :                             | 3/4 |
| • Blade cut :                            | 3/5 |
| • Tear :                                 | 3/4 |
| • Puncture :                             | 3/4 |
| • Cutting by sharp objects (ISO 13997) : | C/F |

#### EN 407 : 2020

- |                                    |     |
|------------------------------------|-----|
| • Flame behavior :                 | 4/4 |
| • Contact heat :                   | 2/4 |
| • Convective heat :                | 2/4 |
| • Radiant heat :                   | X/4 |
| • Small splashes of liquid metal : | 4/4 |
| • Large splashes of liquid metal : | X/4 |

### PROTECTION LIMITS :

- Do not use for handling objects with a temperature higher than 250°C.
- Do not use for handling chemical or liquids products.

### RECOMMENDED USES:

- Gloves specially designed for handling hot or sharp parts, metalworking, automotive...
- Working outdoors in wet weather.

### MAINTENANCE AND STORAGE

- No special maintenance is recommended. It is advisable to store the products in a cool, dry and ventilated place, keep away from light.

### END OF LIFE

- End-of-life destruction must be controlled and comply with European traceability and environmental requirements.

EU type certificate issued in accordance with module B Regulation (EU) 2016/425

LEITAT ON n° : 0162

The EU declaration of conformity is available on

[www.guyard-sa.com](http://www.guyard-sa.com)