



SETRON, cylindrical fuse link, Class CC, 0.8 A, time-lag, Un AC: 600 V, respect national installation rules! for protection of control transformers, reactors and selenoids

Figure similar

Model	
product brand name	SETRON
product designation	Cylindrical fuse link
General technical data	
operating class of the fuse link	Slow
type of voltage of the operating voltage	AC
Main circuit	
operational current rated value	1 A
Product details	
product component striker	No
Mechanical Design	
mounting position	Any, preferably vertical
net weight	8 g
Approvals Certificates	
General Product Approval	other




[Confirmation](#)

Environment

[Environmental Con-
firmations](#)

Further information

Information on the packaging
<https://support.industry.siemens.com/cs/ww/en/view/109813875>
Information- and Downloadcenter (Catalogs, Brochures,...)
<http://www.siemens.com/lowvoltage/catalogs>
Industry Mall (Online ordering system)
<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3NW1008-0HG>
Service&Support (Manuals, Certificates, Characteristics, FAQs,...)
<https://support.industry.siemens.com/cs/ww/en/ps/3NW1008-0HG>
Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)
http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3NW1008-0HG
CAx-Online-Generator
<http://www.siemens.com/cax>



last modified:

5/26/2025 

