

Accessory for SIRIUS 3RM1 Fuse module with GG fuses 20 A for use according to IEC for 22.5 mm attachment adapter 8US1216.., 8US1616.., 8US1716..



Figure similar

General technical data:		
Product brand name		SIRIUS
Product designation		Fuse module
Design of the product		With 3NW6007-1 fuse
Suitability for use		Motor starter 3RM1
Product function Short circuit protection		Yes
Protection class IP		IP20
Installation altitude at height above sea level maximum	m	2 000
Ambient temperature		
• during operation	°C	-25 ... +60
• during transport	°C	-40 ... +70
• during storage	°C	-40 ... +70
Relative humidity during operation	%	10 ... 95
Shock resistance		15g / 11 ms
Vibration resistance		2g
Surge voltage resistance rated value	V	6 000
Insulation voltage rated value	V	690

Reference identifier acc. to DIN EN 81346-2		X
---	--	---

#### Safety related data:

Protection against electrical shock		finger-safe
-------------------------------------	--	-------------




#### Main circuit:

Number of poles for main current circuit		3
Operating voltage rated value maximum	V	500
Relative symmetrical tolerance of the operating voltage	%	10
Operating frequency 1 rated value	Hz	50
Operating frequency 2 rated value	Hz	60
Operating current at AC at 400 V rated value	A	16
Ampacity maximum	A	25
Operating current at AC at 480 V acc. to UL 508	A	16
Power loss [W] for rated value of the current at AC in hot operating state	W	3

#### Installation/ mounting/ dimensions:

Mounting position		any
Mounting type		snap-on mounting
Width	mm	22.5
Height	mm	182.1
Depth	mm	82.5

#### Certificates/approvals

General Product Approval	Declaration of Conformity	Test Certificates	other
 UL		 EG-Konf.	<a href="#">Type Test Certificates/Test Report</a> <a href="#">Confirmation</a>

#### Further information

**Information- and Downloadcenter (Catalogs, Brochures,...)**

<http://www.siemens.com/industrial-controls/catalogs>

**Industry Mall (Online ordering system)**

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mfb=3RM1932-1AB>

**Cax online generator**


<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mfb=3RM1932-1AB>

**Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**

<https://support.industry.siemens.com/cs/ww/en/ps/3RM1932-1AB>

**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)**

[http://www.automation.siemens.com/bilddb/cax\\_de.aspx?mfb=3RM1932-1AB&lang=en](http://www.automation.siemens.com/bilddb/cax_de.aspx?mfb=3RM1932-1AB&lang=en)



last modified:

04/27/2018