

270102010

Taguan 130 flat, closed (with Battery Compartment)

Taguan 130 flat, closed (with Battery Compartment)

Catalogues | Assembly instructions | Declaration of Conformity | Drawing | 3D Data

Technical data

Height	125 mm
Width	80 mm
Depth	36.7 mm
Material	ABS
Colour	ocean blue (RAL 5020)
Ingress protection	IP40
Degree of protection norm	EN 60529
temperature min.	-40 °C
temperature max.	80 °C
Surface resistance	4x10^14 Ohm
Surface resistance norm	IEC 60093
Other versions on request	EMV

Commercial data

Country of origin	RO
Order unit	1 Piece
Customs tarif number	39269097
Weight	0.11 kg
GTIN	4250157916662

ETIM classification

ETIM 8	EC001031

ROSE SYSTEMTECHNIK GMBH
Erbeweg 13-15
32457 Porta Westfalica, Germany

Tel.: +49 571 50 41-0
Fax: +49 571 50 41-6
Mail: rose@rose-pw.de

Accessories

270100900
Taguan Spare screw set

Zubehör - s. Zeichnung
Accessories - see drawing

270102800
Battery holder 4 micro-cells (AAA)

Zubehör - s. Zeichnung
Accessories - see drawing

270102810
Taguan 130 Monoblock holder

Zubehör - s. Zeichnung
Accessories - see drawing

270102820
Taguan 130 Clip

Zubehör - s. Zeichnung
Accessories - see drawing

270102850
Taguan Shaft cover RAL 5020

Zubehör - s. Zeichnung
Accessories - see drawing

270102870
Taguan Shaft cover infrared

Zubehör - s. Zeichnung
Accessories - see drawing

821000010
MEMBRANE KEYPADS FT 130b

Zubehör - s. Zeichnung
Accessories - see drawing

821000020
MEMBRAN KEYPADS FT 130e