



### Main

Range	New Unica
Device application	Mounting
Product or component type	Cover frame
Aesthetic name	Unica
Number of gangs	1 gang
Installation direction	Horizontal
Type of frame	Single
Number of modules	1 module
Fixing mode	Clip-in
Colour tint	White (RAL 9003)

### Complementary


Provided equipment	Fixing frame
Material	Thermoplastic ABS-UV stabilised: cover frame PBT (polybutylene terephthalate): fixing frame
Standards	IEC 60669-1 IEC 60884-1
Width	36 mm
Height	75 mm
Depth	9 mm
Net weight	0.011 kg
Resistance to chemical agents	Resistant to alcohol (70 %) Resistant to alcohol (96 %) Resistant to A-Lactic Acid Resistant to diluted quaternary ammonium Resistant to diluted bleach Resistant to diluted ammonia Resistant to soapy water Resistant to crystal cleaner Resistant to hydrogen peroxide 10 volumes Resistant to hexane

### Environment

IK degree of protection	IK04
IP degree of protection	IP21D

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
Sustainable packaging	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration

Environmental Disclosure	<a href="#"> Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations
Minimum percentage of recycled plastic content	34