

Intro LED

INTRO LED TILT WHITE 6.5W GU10 DIM 830

0053535



Range features

- Luminaire with replaceable Sylvania LED Lamp
- Lamp details : 6.5W / 360LM / Dimmable Beam / Angle 40° / 3000K
- Lamp includes LED driver
- Luminaire is IP23 – Class 2
- Available in fixed or tilt (20°)

LED

PRODUCT OVERVIEW

Ordering number	0053535
Technology	LED
Light colour	Warm white
Average life (Rated) (h)	15000
EAN code	5410288535357
Certifications	CE
Mount	Ceiling recessed
Housing	Steel
CRI (Ra)	80
LOR (%)	100
Beam angle(°)	40
Efficacy (Rated) (lm/w)	47
Voltage (V)	220-240
Colour	White
Included lamp	26804
IP rating	23
IK rating	02

Intro LED

INTRO LED TILT WHITE 6.5W GU10 DIM 830

0053535

DATA TABLE

General data

Technology	LED
Ordering number	0053535
Average life (Rated) (h)	15000
EAN code	5410288535357
Certifications	CE
Mount	Ceiling recessed
Long description	Luminaire with replaceable Sylvania LED Lamp. Lamp details : 6.5W / 360LM / Dimmable Beam / Angle 40° / 3000K . Lamp includes LED driver. Luminaire is IP23 – Class 2. Available in fixed or tilt (20°)
Product name	INTRO LED TILT WHITE 6.5W GU10 DIM 830
Control gear type	Integral
Environment	Interior
General application	Residential accent downlighting
Housing	Steel

Optical data

Light colour	Warm white
CRI (Ra)	80
LOR (%)	100
Beam angle(°)	40
Luminous flux (Nominal) (lm)	360
Distribution type	Direct

Electrical data

Efficacy (Rated) (lm/w)	47
Voltage (V)	220-240
Electrical protection	CLASS II

Intro LED

INTRO LED TILT WHITE 6.5W GU10 DIM 830

0053535

Physical data


Weight (kg)	0.5
Colour	White
Lamp included	Yes
Included lamp	26804
Height (mm)	95
Width (mm)	82
Length (mm)	82
IP rating	23
IK rating	02
Vertical tilt (°)	30
Cutout diameter (mm)	73 ø
Cutout shape	Round
Recessed depth (mm)	95
Reflector material	Bright Aluminium Reflector

Intro LED

INTRO LED TILT WHITE 6.5W GU10 DIM 830

0053535

TECHNICAL DRAWINGS



ENERGY LABEL

