

Circular Saw XGT®

HS009G

40Vmax • 4 000 min⁻¹ • 235 mm

XGT® Battery Powered, Efficient circular saw.

40Vmax XGT® Li-ion battery and brushless motor makes this saw excellent choice for demanding applications. The blade can reach up to 4 000 min⁻¹ to ensure high cutting performance. Auto-Start Wireless System function with bluetooth for remote vacuum start.



Technical specifications

Nominal Battery Voltage	40 V
Voltage XGT	✓
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
Brushless Motor	✓
No load speed	4000 min ⁻¹
Max. Cutting Depth at 90°	85 mm
Max. Cutting Depth at 45°	61 mm
AWS ready	✓
Sound Power Level (L _{WA})	105 dB(A)
Sound Pressure Level (L _{pA})	97 dB(A)
Noise Uncertainty (K Factor)	3 dB(A)
Product Dimensions (L x W x H):	413 x 196 x 316 mm
Tool weight with battery	5,1 - 6,3 kg
Max. Cutting Depth at 60°	44 mm

User benefits

- Lightweight & high power
- Electric brake for maximum productivity and increased operator safety
- Auto-start Wireless System (AWS) connects to compatible vacuum cleaners with Bluetooth
- eXtreme Protection Technology (XPT) is engineered for improved dust and water resistance for operation in harsh conditions
- Battery protection circuit protects against overloading, over-discharging and over-heating

Link to product - www.makitauk.com



Related products

Other

User manual

Parts drawing