



ENGLISH

Datasheet

RS Pro Platform Ladder 5 steps Fibreglass 3.35 to 5.79m open length

RS Stock No: **799-0682**



Product Details

RS Pro platform ladder with 5 steps, is a lightweight professional quality industrial ladder suitable for a range of jobs including multiple sizes of A-frame, 90° ladders, an extension or even as a scaffold system. This little giant horse ladder with fibreglass stiles, has 3.35 to 5.79 m open length and 1.70 m closed length. The multi-purpose ladder meets EN131 standards.

Features and Benefits

- Non conductive fibreglass construction for added protection
- Protective feet to avoid damage to stairs and surfaces and for added stability
- Sturdy flexible hinges and wide legs for further stability
- Glider wheels for easy movement



Specifications:

Closed Length	1.7 m
Ladder Type	Multi-Purpose
Maximum Load	150 kg
Number of Treads	5
Open Length	3.35 to 5.79 m
Stiles Material	Fibreglass
Weight	20.9 kg
Standards Met	EN 131
Step Height	1.63 to 2.74 mm