



ENGLISH

Datasheet

T5 Fluorescent Emergency Exit Sign

RS Stock number: 414-333



Specifications:

Country of Origin:	United Kingdom
CE Mark Compliance:	CE marked REACH and RoHS compliant
Compliance to Standards:	EN60598.2.22: 1999
Manufacturing Quality Approval:	ISO9001: 2008
Luminaire Dimensions:	350mm x 108mm
Housing Construction:	850° C polycarbonate
Body Finish:	White
Protection Degree:	IP65
Insulation Class and Supply Voltage:	Class 1 230/240 50/60Hz
Control Gear manufacturer/type:	P996 inverter/charger
Power Factor Correction:	>0.85
Radio Interference Compliance:	EN55015
Harmonics Compliance:	EN61000-3-2 Class C
Batteries Employed:	3 x 1.5Ah high temp Ni-CAD
Light Distribution Category:	Exit Signage
Lamp Wattage and Type:	Hybec or approved equivalent T5 8W Fluorescent
Lamp Manufacturer:	Hybec (16713)
Average Rated Life:	5000
Initial Lumen Output:	400
CCT (°C):	4000