

40VMax Hedge Trimmer XGT®

UH021G

600 mm

Model UH021G is a cordless hedge trimmer powered by a 40Vmax XGT Li-Ion battery. This machine provides smooth and efficient trimming thanks to the output power and number of strokes.

Feature and benefits: Constant speed control suppresses rotation drop to enable stable trimming, Lightweight design, Reverse function to clear jams, Single sided blade and triple-ground teeth.



Technical specifications

Voltage XGT	✓
Nominal Battery Voltage	40 V
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
Strokes per Minute (SPM)	4200 min ⁻¹
No load speed	2100 min ⁻¹
Length Of Blade	600 mm
Max blade opening	20 mm
Tooth Spacing	30 mm
Continuous Use XGT® 40V Max / 4.0 Ah	105
Brushless Motor	✓
Sound Power Level (L _{WA})	93 dB(A)
Sound Pressure Level (L _{pA})	83 dB(A)
Noise Uncertainty (K Factor)	3 dB(A)
Vibration Level, Hedge Trimming	≤ 2,5 / ≤ 2,5 m/s ²

User benefits

- Anti-restart function minimises accidental start-up
- Electric brake for maximum productivity and increased operator safety
- eXtreme Protection Technology (XPT) is engineered for improved dust and water resistance for operation in harsh conditions

Link to product - www.makita.uk.com



Related products

Other

User manual

Parts drawing