

Datasheet

Stock No: 183-9231

RS Pro Single Core Harsh Environment Wire 500m 1 Strand



Product Details

1 / 0.8 Solid Strand Wire BS6004

Solid conductor wire manufactured in accordance with BS6004 Table 9. The plain annealed copper conductor is insulated with heat resisting PVC. A continuous temperature rating of 85°C makes the wire suitable for a range of applications including lighting. BASEC approved. Cable ref. no. cable colours white, blue and brown are harmonised type. This excludes cable colour yellow/green.

Specifications:

Sheath Colour	White
Insulation Material	PVC
Resistant To	Heat
Core Strands	1/0.8 mm
Maximum Operating Temperature	+85°C
Operating Temperature Range	Maximum of +85 °C
Length	500m
Size of Strands	0.8 mm
Conductor Material	Bare Annealed Copper
Number of Strands	1
Cable Shape	Single Core