

## Features

- S092.103 fitted with a 3D Flex system allowing to work, even when tilted upside down. Thanks to this solution, you can reach the most inaccessible areas with unprecedented ease.
- High-pressure tank
- White colour for easy localisation in a workshop

## RS PRO Pressure Sprayers ALKA Line

RS Stock No.: 0708695, 0708696, 0708698, 0708699



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## Product Description

## RS PRO ALKA Pressure Sprayers with capacities from 1.5 litres up to 12 litres.

The RS PRO sprayers are characterised by exceptional quality and attention to detail. All Alka Line pressure sprayers have a pressure of 4 bar, which makes spraying easier and the pressure more stable. All tanks have a 5-year warranty.

- The 1.5 litres sprayer (0708695), comes with a 3D-flex system, adjustable nozzle and very ergonomic smart bottle shape and dosing valve lock. An alkalis-proof sprayer is light and handy.
- The 5, 9 and 12 litres sprayers (0708696, 0708698, 0708699) come with a lance with jet regulation, dosing valve lock, three-layer reinforced hose and efficient high-pressure pump.

### Technical specification:

| Stock No. | Sprayer Type        | Capacity (L) | For Use With | Colour | Working Pressure (bar) |
|-----------|---------------------|--------------|--------------|--------|------------------------|
| 0708695   | Handheld            | 1.5          | Alkalis      | White  | 4                      |
| 0708696   | Handheld / Shoulder | 5            | Alkalis      | White  | 4                      |
| 0708698   | Handheld / Shoulder | 9            | Alkalis      | White  | 4                      |
| 0708699   | Handheld / Shoulder | 12           | Alkalis      | White  | 4                      |

Similar products:

## Acid-Proof Pressure Sprayers

| Stock No. | Sprayer Type        | Capacity (L) | For Use With | Colour | Working Pressure (bar) |
|-----------|---------------------|--------------|--------------|--------|------------------------|
| 0708691   | Handheld            | 1.5          | Acids        | White  | 4                      |
| 0708692   | Handheld / Shoulder | 5            | Acids        | White  | 4                      |
| 0708693   | Handheld / Shoulder | 9            | Acids        | White  | 4                      |
| 0708694   | Handheld / Shoulder | 12           | Acids        | White  | 4                      |

## BASIC Line Pressure Sprayers

| Stock No. | Sprayer Type        | Capacity (L) | For Use With                  | Colour | Working Pressure (bar) |
|-----------|---------------------|--------------|-------------------------------|--------|------------------------|
| 0708700   | Handheld            | 1.5          | Neutral Products / Pesticides | Green  | 4                      |
| 0708701   | Handheld / Shoulder | 5            | Neutral Products / Pesticides | Green  | 4                      |
| 0708702   | Handheld / Shoulder | 9            | Neutral Products / Pesticides | Green  | 4                      |
| 0708703   | Handheld / Shoulder | 12           | Neutral Products / Pesticides | Green  | 4                      |