



tesa® 60428

Product Information



Premium PVC surface protection and masking tape

Product Description

tesa® 60428 is a mechanical and chemical resistant PVC, coated with a low strength natural rubber adhesive. This tape is tear resistant and easy to remove, and can be applied outdoors for a maximum duration of 3 months. The storage time after application should not exceed one year.

The product design of tesa® 60428 allows convenient application by hand and it is also suitable for converting and die cutting.

Main features:

- High mechanical and chemical resistance
- Easy to apply and residue-free removal
- Thin and conformable
- Suitable for converting and die cutting
- UV resistant for 3 months

Application Fields

- Wide range of masking requirements
- Converting and die cutting

To ensure the highest performance possible, our aim is to fully understand your application (including the substrates involved) in order to provide the right product recommendation.

Technical Information (average values)

The values in this section should be considered representative or typical only and should not be used for specification purposes.

Product Construction

- | | | | |
|--------------------|----------------|-------------------|-------|
| • Backing material | PVC film | • Total thickness | 60 µm |
| • Type of adhesive | natural rubber | | |

Properties/Performance Values

- | | | | |
|-----------------------|---------|-------------------------|-----|
| • Elongation at break | 78 % | • Automatic application | no |
| • Tensile strength | 43 N/cm | • Easy to remove | yes |

Adhesion to Values

- | | |
|---------|----------|
| • steel | 0.3 N/cm |
|---------|----------|

For latest information on this product please visit <http://l.tesa.com/?ip=60428>



tesa[®] 60428

Product Information

Disclaimer

tesa[®] products prove their impressive quality day in, day out in demanding conditions and are regularly subjected to strict controls. All information and recommendations are provided to the best of our knowledge on the basis of our practical experience. Nevertheless tesa SE can make no warranties, express or implied, including, but not limited to any implied warranty of merchantability or fitness for a particular purpose. Therefore, the user is responsible for determining whether the tesa[®] product is fit for a particular purpose and suitable for the user's method of application. If you are in any doubt, our technical support staff will be glad to support you.

For latest information on this product please visit <http://l.tesa.com/?ip=60428>