

"Multi-purpose" click wrenches

SERIES 208

CLICK WRENCH

"MULTI-PURPOSE"

ISO 6789 TYPE II - CLASS A THE COMPACT WRENCH FOR ALL APPLICATIONS

HEAVY-DUTY

- Reliability of mechanism tested to 25000 cycles.
- Resistant to all hydrocarbons for use in garages or industrial environments.

Reliable

- Accurate to within $\pm 4\%$ in accordance with ISO 6789.
- Long-lasting accuracy.
- Double (coarse and fine) vernier adjustment.




■ J-S.208D - Click wrenches without accessories



NF EN ISO 6789, ISO 6789, DIN EN ISO 6789

- Accuracy: $\pm 4\%$.
- Reliability of mechanism 25 000 cycles.
- End fitting: 9 x 12 or 14 x 18 mm for accessories (ratchets, polygon and open end bits).
- One-way wrenches usable for unscrewing by reversing the bits.
- Sensitive and sound click when reaching torque.
- Automatic reset.
- Supplied with ISO 6789 calibration certificate.
- Supplied in plastic protection tube.

	Capacity [N.m]	Attachment	Graduation [N.m]	L [mm]	$\Delta\Delta$ [kg]
J.208-50D	10 - 50	9 x 12	0,5	337	0,780
S.208-100D	20 - 100	9 x 12	1,0	396	0,920
S.208-200D	40 - 200	14 x 18	2,0	466	1,110
S.208-340D	60 - 340	14 x 18	2,0	618	1,430