
SBBSM127P Proto Advantage

Datasheet revision 1.0 www.Proto-Advantage.com

Surface mount breadboard 2x2" 1.27mm pitch SMT pads



Product Highlights

Surface mount solder breadboard
Immersion Gold (ENIG) Finish
Single Sided
1443 pads in total
Surface mount pads on 1.27mm matrix on one side
Pad pitch of 1.27mm center-to-center
37 rows, 39 columns

Specifications

Dimensions:	2.0" x 2.0" x 0.0625"
PCB construction:	FR-4 UL94V-0
PCB operating temperature range:	-40°C to +130°C
PCB reflow maximum temperature:	+260°C
Pad size:	Square: 1.0mm x 1.0mm (0.039" x 0.039")
Pad pitch:	1.27mm center-to-center
Space between pads:	0.27mm (0.011")

© 2007-2024 Proto Advantage ® Inc.