

Product availability: Stock - Normally stocked in distribution facility

### Main

Commercial Status	Commercialised
Range	Lineryg
Product name	FT
Device short name	GV2G
Product or component type	Comb busbar
Accessory / separate part category	Connection accessory
Poles description	3P
Range compatibility	TeSys - U TeSys - K TeSys - GV2 TeSys - D
Number of tap-offs	4
[I <sub>th</sub> ] conventional free air thermal current	63 A
Connection pitch	2.13 in (54 mm)

### Complementary

Mounting location	On terminal
[Ui] rated insulation voltage	690 V
Product weight	0.19 lb(US) (0.085 kg)

### Ordering and shipping details

Category	22367 - MANUAL STR PROTECTOR - GV2
Discount Schedule	I11
GTIN	00785901490104
Nbr. of units in pkg.	1
Package weight(Lbs)	0.19
Product availability	Stock - Normally stocked in distribution facility
Returnability	Y
Country of origin	FR

### Contractual warranty

Period	18 months
--------	-----------

The information provided in this documentation contains general descriptions and/or technical characteristics of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.