



2 YEARS
MANUFACTURER
GUARANTEE



Product number 1507071
EAN 3281855070715

DESCRIPTION

- 3 socket adapters with 1 remote receiver for indoor use IP 20.
- Switching status display on the receiver, can also be operated manually.
- Simple and flexible use through self-learning coding.
- Fail-safe through more than 65,000 different codes.
- Permanent storage of the coding even during a longer power failure.
- 3-channel handheld transmitter for universal control of single or multiple receivers simultaneously.
- Switching capacity 2.300 W.
- Range up to 25 meters (frequency 433.92 MHz).
- Including 1x 3 V battery (type CR2032) for the handheld transmitter.
- Sockets with increased touch protection.

TECHNICAL DATA

Number of batteries	1	Wireless range	25 m
Battery type	CR 2032	Max. current carrying capacity	10 A
Battery technology	Lithium	Degree of protection (IP)	IP20
Radio frequency	433 MHz	Colour	White

PACKAGING, DIMENSIONS AND WEIGHTS

Packaging	In display packaging	Dimension LxWxH (without packing)	5.1 cm x 14.8 cm x 10 cm
UP	1	Weight of product (including packaging)	0.27 kg
Weight of product (without packaging)	0.21 kg	Dimension LxWxH (incl. packing)	5.5 cm x 15 cm x 10 cm