

Features

- Transparent green polycarbonate housing UL94 – V0
- Funnel cable entry
- Screw clamp
- Peak operational temperature of 85°C
- Brass Clamp with wire protection
- Screwmateral: galvanized steel
- High mechanical resistance with good electrical characteristics

RS PRO Non-Fused Terminal Block, 1-Way, 35mm²Wire, Screw Termination

RS Stock No.: 0642820



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

RS PRO Non-Fused Terminal Block

RS Pro non-fused terminal block is designed for termination or the joining of cable ends. This 1-way polycarbonate terminal block with 35-mm² wire, features screw termination. The panel mount terminal block with brass contact, has a voltage rating of 450 V.

This terminal block meets EN 60998-1: 2004 and EN 60998-2-1: 2004 standards.

General Specifications

Number of Ways	1
Wire Size	35mm ²
Termination Method	Screw
Fused	No
Material	PC
Voltage Rating	450 V
Maximum Operating Temperature	+85°C
Enclosed	Yes
Contact Material	Brass

Approvals

Declarations	REACH DoC
Standards Met	EN 60998-1: 2004 EN 60998-2-1: 2004

Similar Products

Stock No.	Brand	Product Name	No. of Ways	Wire Size	Termination Method
0642819	RS PRO	Non-Fused Terminal Block	1	25mm ²	Screw
0642820	RS PRO	Non-Fused Terminal Block	1	35mm ²	Screw