



ENGLISH

Datasheet

Nitrile Rubber O-Ring Cord, 2.4mm Diam. , 8.5m Long

RS Stock number 1591484



Features

Nitrile O-Ring Splicing Kit

Nitrile NBR70 splicing kit for fast, on the spot production of O-Rings, reducing down time. Replacement Nitrile O-Ring cord is available separately, from 1.6mm to 8.4mm diameter.

Nitrile (NBR) is suitable for use within applications running at a maximum continuous temperature of 120°C (or up to 150°C intermittently). Use below -30°C requires special consideration.

Note

Each size of O-Ring cord is sold per reel of 8.5m.

O-Ring Kits

Precisely engineered Imperial and Metric O-Rings in kit form, manufactured from materials including Viton®, Nitrile rubber and FPM.