

Features

- Clean and neat finish
- Rapid installation
- No tools needed
- Firmly locks into place
- Will not corrode

RS PRO Rivets

RS Stock No.: See Table



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

- These drive rivets are a multi-purpose, front loaded fastener
- They have a hollow body which increases their flexibility for ease of insertion
- Ideal for light fixing applications such as decorative trim and name plates
- Can be used as a decorative hole plug
- No installation tooling needed

Material Specifications

Rivet Body Material	Acetal (POM)
Finish	Plain
Rivet Type	Snap
Colour	Natural
Flammability Rating	UL94HB
Working Temperature Range	-30°C to +90°C

Part Specifications

Parameters	0304044	0304045	0304047	0304048	0304049	0304050
G (Fixing Hole Diameter)	3.2mm	3.9mm	4.7mm	5.5mm	6.4mm	7.8mm
T (Panel Thickness)	1.0-4.5	1.0-5.0	1.0-5.5	6.0-9.0	1.5-6.5	1.5-7.0
D ±0.25 (Head Diameter)	8.0mm	9.0mm	10.0mm	12.0mm	12.0mm	14.0mm
H ±0.25 (Head Height)	1.5mm	1.6mm	1.7mm	2.0mm	2.0mm	2.2mm
L (Rivet Length)	13.0mm	14.0mm	15.0mm	18.0mm	17.0mm	19.0mm
W (Body Thickness)	2.7mm	2.9mm	3.4mm	3.8mm	3.9mm	4.2mm

