

Features

- 6 UK sockets with surge filter
- Tough aluminium extrusion
- Metal legs with screw hole fixing
- Shrouded switch with switch cover
- 3-metre 1.5mm lead
- Ideal for tougher working environments such as a workbench or laboratory

RS PRO Power Distribution Unit – Type G, 6 Gang PDU, 3m Cable, 6A

RS Stock No.: 839-9800



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

This RS PRO Surge Protected 6 Gang Power Distribution Unit is designed for safe and efficient power distribution in professional and industrial environments. It features six Type G (British) sockets and a 3-meter cord, making it ideal for use in offices, workshops, server rooms, and data centres. The unit is switchable and includes a power indicator for added convenience and safety.

Applications:

- Suitable for powering multiple devices in office setups, labs, and industrial environments.*
- Ideal for use with computers, networking equipment, and other electronics.*
- Not recommended for outdoor use or environments with high moisture exposure.*

General Specifications

Body	Plastic
------	---------

Mechanical Specifications

Colour	Black
Mounting Type	Horizontal or Vertical

Electrical Specifications

Number of Sockets	6
Socket Type	Type G - British
Cord Length	3m
Switchable	Yes
Corded	Yes
Power Indicator	Yes
Current Rating	6A, 16A

Similar Products

Stock No.	Brand	Product Name
161-7254	RS PRO	Type G - British 6 Gang Power Distribution Unit, 3m Cable, 13A, 250 V ac
839-9800	RS PRO	Type G - British 6 Gang Power Distribution Unit, 3m Cable, 6A
161-7253	RS PRO	Type G - British 4 Gang Power Distribution Unit, 3m Cable, 13A, 250 V ac
839-9806	RS PRO	Type G - British 6 Gang Power Distribution Unit, 3m Cable
839-9799	RS PRO	Type G - British 4 Gang Power Distribution Unit, 0.5m Cable
161-7268	RS PRO	Type G - British 12 Gang Power Distribution Unit, 3m Cable, 13A, 250 V ac
839-9787	RS PRO	Type G - British 4 Gang Power Distribution Unit, 0.15m Cable, Fused
839-9796	RS PRO	Type G - British 4 Gang Power Distribution Unit, 1m Cable, 230V, Fused
161-7270	RS PRO	Type G - British 16 Gang Power Distribution Unit, 3m Cable, 13A, 250 V ac
161-7266	RS PRO	IEC C13 12 Gang Power Distribution Unit, 3m Cable, 10A, 250 V ac
161-7275	RS PRO	NF Euro Socket 12 Gang Power Distribution Unit, 3m Cable, 16A, 250 V ac
161-7257	RS PRO	Type G - British 6 Gang Power Distribution Unit, 3m Cable, 32A, 250 V ac
161-7256	RS PRO	Type G - British 6 Gang Power Distribution Unit, 3m Cable, 16A, 250 V ac
161-7284	RS PRO	IEC C13 12 Gang Power Distribution Unit, 3m Cable, 13A, 250 V ac
374-137	RS PRO	IEC C13 10 Gang Power Distribution Unit, 2m Cable, 10A, 230 V AC RCD Protected, Fused
161-7261	RS PRO	Type F - German Schuko 6 Gang Power Distribution Unit, 3m Cable, 16A, 250 V ac
374-143	RS PRO	IEC C13 6 Gang Power Distribution Unit, 2m Cable, 10A, 250 V ac, Fused
472-6469	RS PRO	IEC C13 12 Gang Power Distribution Unit, 20A, 250 V, Fused
755-3983	RS PRO	Type E - French 5 Gang Power Distribution Unit, 2.5m Cable, 16A, 230 V ac
161-7274	RS PRO	Type F - German Schuko 24 Gang Power Distribution Unit, 3m Cable, 16A, 250 V ac