

Metal tool box with assortment, 143 pieces 1/4 " + 3/8", inch sizes, 1483KHD3RB-FF2



Article number: 1483KHD3RB-FF1

Size: 523x257x300cm

Weight: 11,000 g

Packing quantity: 1pc. "

143-piece Metal tool case with range 1/4 " + 3/8".

- For aircraft mechanics
- Suitable for all major aircraft types
- Especially suitable for maintenance 1/4 ", 3/8"

Lid Compartment – 5 pieces



481-400 Hammer	400g
3625N-35 Superflex plastic hammer	415g
2509 Flexible gripper	525 mm
2535F2 Magnetic lifter	1kg
7762 Extension 3/8 "	250mm

Foam insert socket wrench 1/4 ", 3/8", 98-piece



Ratchet 1/4 ", narrow head	6950SL	-
Ratchet 3/8 ", narrow head	7750SL	-
Renewals 1/4 "	6960/6962	50, 150 mm
Renewals 3/8 "	7760/7761	75, 125 mm
Drive handle 1/4 "	6956	-
Crank 3/8 "	7752	-
Universal joint 1/4 "	6966	-
Universal joint 3/8 "	7766	-
3/8 "to 1/4" transitional part	7764	-
1/4 "to 3/8" transitional part	7765	-
3/8 "to 1/2" transitional part	8164-1 / 2	-
Bit holder 1/4 "	6972H	-
Bit holder 3/8 "	7407H	1/4 "- 3/8"
Sockets 1/4 ", double	A6700DZ	3/16 ", 7/32", 1/4 ", 9/32", 5/16 ", 11/32", 3/8 ", 7/16", 1/2 ", 9/16"
Joint Sockets 1/4 ", double	A6710DZ	1/4 ", 5/16", 11/32 ", 3/8", 7/16 "
Sockets 1/4 ", double	A6800DZ	3/16 ", 7/32", 1/4 ", 9/32", 5/16 ", 11/32", 3/8 ", 7/16", 1/2 ", 9/16"
Sockets 1/4 ", double, long	A6800DM-4	4 mm
Sockets 3/8 ", Double, shortly	A7400DZ	1/2 ", 17/32", 9/16 ", 19/32", 5/8 ", 11/16", 3/4 ", 13/16"
Angle screwdriver set, Hexagon,12-piece	BE-9780	0.050 ", 1/16", 5/64 ", 3/32", 7/64 ", 1/8", 9/64 ", 5/32", 3/16 ", 7/32", 1 / 4 ", 5/16"
Bit set and TORQ-SET® screws 28-piece	59 / S28-4	
Bit TORQ-SET® screws 1/4 "	59S / TS-1/4	-
Bit TORQ-SET	70S / TS1 / 4 1/4 "	
Ergo Adjustable Wrench 8 "	9071C	-
Screwdriver	808 050	-
Bit-ratchet 1/4 "	2058-BR	-
Feeler gauges	1544	-
ERGO Cuttermesser	KE18-01	-

15 pieces



Cranked screwdriver for slotted screws	2047-1-5.5	1x5, 5x125 mm
Double angled offset screwdriver for Phillips screws	2047PR-1-2	PH 1-2
Ergo screwdriver for slotted screws	BE-8030	0,6x3,5x75
Ergo screwdriver for slotted screws	BE-8155	1,2x6,5x125
Ergo screwdriver for slotted screws	BE-8150	1,0x5, 5x100 mm
Ergo screwdriver for slotted screws, hex shaft and approach	BE-8260	1,6x8,0x175
Ergo Screwdriver for slotted screws, short version	BE-8350	1x5,5x25
Ergo Screwdriver for Phillips screws, short version	BE-8602	PH2x25
Ergo screwdriver	BE-8610/BE-8620	PH1x75, PH2x100
Telescopic articulated mirror	5515T-52	Ø 50 mm
Scribe cranked	1177-SCRIBE	230mm
Flexible scale, stainless	1179-FLX-2	300 mm
Precision screwdriver	704Z-3/32	3 / 32x75

11 pieces



Tape measure	MTB-3-16-E	3m
Ergo side cutter	2101 GC-160IP	160mm
Ergo nose pliers angled,	2427 GC-200 IP	200mm
Wire twisting pliers	2855	224mm
Ergo Water Pump Pliers	8224CIP	-
Connector pliers	2650	-
Ergo Combination Pliers	2628 GC-160IP	160mm
Combined Puller & spreader	2632	170mm
Screwdriver	3734	Ø 3, 5, 8mm

23 pieces



Ratchet ring spanner	1320RZ	1 / 4x5 / 16 ", 5 / 16x11 / 32 ", 3 / 8x7 / 16 " 1 / 2x9 / 16 "
Open-ended spanner	6Z	1 / 4x5 / 16 ", 5 / 16x11 / 32 ", 3 / 8x7 / 16 ", 1 / 2x9 / 16 ", 19 / 32x11 / 16 ", 5 / 8x3 / 4 ", 13 / 16x7 / 8 "
Combination spanner cranked	1952Z	1/4 ", 5/16", 11/32 ", 3/8", 7/16 ", 1/2", 9/16 ", 5/8", 11/16, 3/4 ", 13 / 16 ", 7/8"

