



ENGLISH

Datasheet

Stock No. 161-7288

## RS PRO Ammeter retrofit module for PDU



Long press Button to set Bell On/Off

If you set Bell on, when current is over 32 A, bell will ring



## **SPECIFICATIONS:**

### **Input**

Rating voltage: 250 V ac 50/60 Hz

### **Display**

Operation state: 1 LED indicator

Load current:

1. Full scale: 32 A
2. Accuracy: +/-1%+1 Digit
3. Resolution: 100 mA
4. Response time: 400 ms

Input voltage

1. Full scale: 255 V
2. Accuracy: +/-1%+3 Digit
3. Resolution: 1 V
4. Response time: 400 ms

### **Controlling Button**

BUTTON: Switch over display information

### **Module outlook**

Dimension: L x W x H = 140 x 42 x 57 mm

Color: Black

### **Working environment**

Operating Temperature: 0 - 50°C,

Relative humidity: 0 - 95%

### **Applications:**

It is widely applied to the data centers of industries like network communication, telecom, electric power, finance, insurance, aerospace, transportation, information processing, education, medical, E-government etc.

10/11/2017