

## Datasheet

### Barrier Strip, 9.52mm Pitch, 1 Row, 15A, 750 V dc

RS Stock 794-8612



## Specification

### Technical Data

- Number Of Ways: 2 to 12
- Current Rating: 15 amps
- Working Voltage: 750 V d.c or a.c. peak
- Insulation resistance: Greater than 10,000 megaohms
- Temperature Range: -55°C to + 100°C

### Materials and finishes

- Moulding: High impact thermoplastic UL 94V-0 rated
- Terminal Plates: Brass, nickel plated
- Terminal Tags: Brass, tin plated
- Screws: 6/32 UNC Binder head, nickel plated
- RoHS Compliant