

## M23 07 Female -soldered contact



Image is for illustration purposes only. Please refer to product description.

|                    |   |
|--------------------|---|
| Part number        | 09 15 107 2703  |
| Specification      | M23 07 Female -soldered contact   |
| HARTING eCatalogue | <a href="https://harting.com/09151072703">https://harting.com/09151072703</a> |

### Identification

|                |                         |
|----------------|-------------------------|
| Category       | Inserts                 |
| Series         | Circular connectors M23 |
| Identification | Signal                  |
| Element        | Inserts                 |

### Version

|                    |  |
|--------------------|--|
| Termination method | PCB solder termination   |
| Gender             | Female   |
| Number of contacts | 7  |
| Details            | Suitable for bulkhead mounted housings 09 15 100 0301, 0302, 0305, 0306 and 0307 only! |

### Technical characteristics

|                       |                   |
|-----------------------|-------------------|
| Rated current         | 20 A              |
| Rated voltage         | 300 V             |
| Rated impulse voltage | 2.5 kV            |
| Pollution degree      | 3                 |
| Insulation resistance | $>10^{10} \Omega$ |
| Limiting temperature  | -40 ... +125 °C   |
| Mating cycles         | $\geq 500$        |

### Material properties

|                   |                |
|-------------------|----------------|
| Material (insert) | Polyamide (PA) |
|-------------------|----------------|



Pushing Performance  
Since 1945

## Material properties

|   |  |
|---|--|
| Colour (insert)                           | White  |
| Material (contacts)                       | Copper alloy   |
| Surface (contacts)                        | Gold plated  |
| Material flammability class acc. to UL 94 | V-0  |
| RoHS                                      | compliant with exemption                               |
| RoHS exemptions                           | 6(c): Copper alloy containing up to 4 % lead by weight |
| ELV status                                | compliant with exemption                               |
| China RoHS                                | 50   |
| REACH Annex XVII substances               | Not contained  |
| REACH ANNEX XIV substances                | Not contained  |
| REACH SVHC substances                     | Yes  |
| REACH SVHC substances                     | Lead   |
| ECHA SCIP number                          | 052d6da0-30ef-44e8-bbe4-e75780521d22                   |
| California Proposition 65 substances      | Yes  |
| California Proposition 65 substances      | Lead   |

## Specifications and approvals

|          |                       |
|----------|-----------------------|
| UL / CSA | UL 1977 ECBT2.E235076 |
|----------|-----------------------|

## Commercial data

|                                |   |
|--------------------------------|---|
| Packaging size                 | 5   |
| Net weight                     | 9 g   |
| Country of origin              | Germany   |
| European customs tariff number | 85366990  |
| GTIN                           | 5713140187276                                   |
| eCl@ss                         | 27440223 Contact insert for circular connectors |
| ETIM                           | EC003557  |
| UNSPSC 24.0                    | 39121421  |