

ISOLATOR 125A DOUBLE POLE



Figure similar

Model	
Product brand name	SENTRON
Product designation	On/Off switches
Type of light source	Not applicable
Mounting type / for light source	Not applicable
Design of the switching function	Switch disconnecter
General technical data	
Number of poles	2
Short-circuit current rating	10 kA
Type of voltage	AC
Protection class	
Protection class IP	Other
Switching capacity	
Switching capacity current / rated value	0.375 kA
Main circuit	
Operating voltage / rated value	440 V

Operating current / rated value	125 A
---------------------------------	-------

Appearance

Color / of the lens	Not applicable
---------------------	----------------

Product details

Product component / Signal lamp	No
---------------------------------	----

Product function

Product function / positive opening (acc. to DIN VDE 0113)	No
--	----

Number

Number of NC contacts	0
Number of NO contacts	2
Number of CO contacts	0

Mechanical Design

Height	89.8 mm
Depth	74.5 mm
Installation depth	70 mm
Number of width units	2

General Product Approval

Declaration of Conformity



Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=5TL1292-0>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/5TL1292-0>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=5TL1292-0

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>

