

## FEATURES

- **Sintered Bronze Material:** Provides excellent wear resistance and durability
- **Flanged Design:** Ensures easy installation and secure fit
- **Dynamic Load Rating of 14 N/mm<sup>2</sup>:** Suitable for dynamic applications
- **Static Load Rating of 50 N/mm<sup>2</sup>:** Handles high static loads effectively
- **ISO 2795 and ISO 9001:2008 Certified:** Meets international quality and performance standards

## RS PRO 30.02 mm Flanged Plain Bearing

RS Stock No: 558-480



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## Product Description

This RS PRO flanged plain bearing is designed for applications requiring reliable and efficient rotational movement. Made from sintered bronze, it offers excellent wear resistance and is ideal for use in environments where lubrication is minimal. The bearing's flanged design ensures easy installation and secure positioning, making it a versatile choice for various industrial applications.

## General Specifications

Bore Size	30.02 mm
Dynamic Load Rating	14 N/mm <sup>2</sup>
Product Type	Plain Bearing
Static Load Rating	50 N/mm <sup>2</sup>
Sub Type	Flanged

## Mechanical Specifications

Material	Sintered Bronze
Outside Diameter	38.06 mm
Width	25 mm

## Approvals

Standards/Approvals	ISO 2795, ISO 9001:2008, UKAS 001
---------------------	-----------------------------------