



Datasheet

RS Pro Yellow Steel Lockable 2 Doors Hazardous Substance Cabinet



RS Stock No: 3147657



ENGLISH

All our range of Hazardous Storage Cabinets are designed to provide safe storage of Flammable Liquids, Chemicals, Paints, Pesticide and other Hazardous Substances.

- **Constructed in 1.2mm thick mild steel, with welded seams**
- **Door is reinforced to prevent distortion.**
- **Chrome Plated 'L' Handle with 2 keys.**
2 point steel locking mechanism
- **Sump Details;**
 - Integral non removable spillage sump in the base of the cabinet to contain major spills
 - Sump Size: H100 x W915 x D457mm
 - Maximum Sump Capacity: 41 Litres
- **Epoxy powder coated finished**
- **Supplied with 1 fully welded shelf tray**
 - Perforated drainage holes in shelf tray to allow spillages to drain into sump.
 - Shelf Size: W915 x D459mm.
 - Each Shelf Capacity 35Kg (U.D.L)
 - Fully adjustable in 25mm increments.



Cabinet Size: H915 x W915 x D459mm



CABINETS COMPLY TO THE FOLLOWING;

- The guide lines set out in the Health and Safety Executive Guide HSG51 for the Storage of Flammable Liquids in Containers.
- The Highly Flammable Liquids and Liquid Gases Regulations, Section 5 (1.D) and the guide to regulation No.5 (17).
- The factory inspectorates Certificate of Approval No.1 parts 3 and 4.
- The Dangerous Substances and Explosive Atmospheres Regulations (DSEAR) Approved Code of Practice (ACoP)L136 paragraphs 94-96 along with Appendices A & B and paragraph 104 which details the performance requirements for fire resisting cupboards and bins. It is however important to emphasise that they do not specify an absolute test or standard for the cabinets or bins, rather they relate to the nominal construction principles.

CABINET
SUPPLIED
WITH
WARNING
LABELS

